




# Claim Enhancements for Falcon® Serological Pipets

**FALCON®**

A Corning Brand

We are pleased to announce three claim enhancements to our Falcon serological pipet portfolio. In the spirit of continuously evolving to support the changing needs of our customers, we are implementing upgrades in the form of a human DNA-free claim, availability of extractables data, and increased sterility.



## Human DNA-free

Falcon serological pipets will now feature a human DNA-free claim.

Pipets will be tested by DNA detection assay per ISO 18385 and found to be free of detectable human DNA.

## Extractables data

Extractables analysis will be conducted in accordance with USP <665>. Data will be made available upon customer request.


## Sterility Assurance Level (SAL) of $10^{-6}$

The serological pipets are sterilized and dosimetrically released per the requirements of ANSI/AAMI/ISO 11137.

The sterility of the upgraded products will be increased from SAL of  $10^{-3}$  to  $10^{-6}$ .



## Ordering Information



### Falcon® Advantage® Packaging, Individually Wrapped

Cat. No.	Size (mL)	Increments (mL)	Overall Capacity (mL)	Color Code	Qty/Pk	Qty/Cs
356521	1	0.01	0.4	Yellow	100	1,000
356507	2	0.01	0.8	Green	100	1,000
356543	5	0.1	2.5	Blue	50	200
356551	10	0.1	3.0	Red	50	200
356525	25, Space Saver	0.25	7.0	Purple	50	200
356535	25, Extended	0.5	11.0	Purple	50	200
356550	50	1.0	10.0	Black	25	100
357600	100	1.0	15.0	Black	5	50

### Paper/Plastic Thermoform Packaging, Individually Wrapped

357521	1	0.01	0.4	Yellow	100	1,000
357507	2	0.01	0.8	Green	100	1,000
357543	5	0.1	2.5	Blue	50	200
357551	10	0.1	3.0	Red	50	200
357525	25, Space Saver	0.25	7.0	Purple	50	200
357535	25, Extended	0.5	11.0	Purple	50	200
357550	50	1.0	10.0	Black	25	100

### Bulk Packaged

357506	1	0.01	0.4	Yellow	100	1,000
357508	2	0.01	0.8	Green	100	1,000
357529	5	0.1	2.5	Blue	50	200
357530	10	0.1	3.0	Red	50	200
357515	25, Space Saver	0.25	7.0	Purple	50	200

## Related Products

### Falcon Pipet Controller

- ▶ LCD display for continuous visualization of speed, modes, and battery status
- ▶ Falcon pipet graduation alignment system (arrow on the nose piece)
- ▶ Well-positioned function buttons
- ▶ 2-position charging stand

Cat. No.	Description
357469	Falcon Pipet Controller, with two 0.2 µm filters and two 0.45 µm filters, two-position charging stand, universal power supply, and set of 3 batteries

## Literature Available

- ▶ Falcon Pipet Controller (CLS-DL-LH-364)
- ▶ Liquid Handling Ergonomics in Every Step (CLS-LH-370)
- ▶ Top 10 Ways to Reduce Contamination Risk (MISC-Contamination Graphic-16)
- ▶ Controlling Cell Culture Contamination (PST-Cell-Contamination-16)

**Warranty/Disclaimer:** Unless otherwise specified, all products are for research use or general laboratory use only.\* Not intended for use in diagnostic or therapeutic procedures. Not for use in humans. These products are not intended to mitigate the presence of microorganisms on surfaces or in the environment, where such organisms can be deleterious to humans or the environment. Corning Life Sciences makes no claims regarding the performance of these products for clinical or diagnostic applications. \*For a listing of US medical devices, regulatory classifications or specific information on claims, visit [www.corning.com/resources](http://www.corning.com/resources).

*Corning's products are not specifically designed and tested for diagnostic testing. Many Corning products, though not specific for diagnostic testing, can be used in the workflow and preparation of the test at the customers discretion. Customers may use these products to support their claims. We cannot make any claims or statements that our products are approved for diagnostic testing either directly or indirectly. The customer is responsible for any testing, validation, and/or regulatory submissions that may be required to support the safety and efficacy of their intended application.*

# CORNING

Corning Incorporated  
Life Sciences

[www.corning.com/lifesciences](http://www.corning.com/lifesciences)

## NORTH AMERICA

t 800.492.1110  
t 978.442.2200

## ASIA/PACIFIC

Australia/New Zealand  
t 61 427286832

Chinese Mainland  
t 86 21 3338 4338

## India

t 91 124 4604000

## Japan

t 81 3-3586 1996

## Korea

t 82 2-796-9500

## Singapore

t 65 6572-9740

## Taiwan

t 886 2-2716-0338

## EUROPE

CSEurope@corning.com

## France

t 0800 916 882

## Germany

t 0800 101 1153

## The Netherlands

t 020 655 79 28

## United Kingdom

t 0800 376 8660

## All Other European Countries

t +31 (0) 206 59 60 51

## LATIN AMERICA

grupoLA@corning.com

## Brazil

t 55 (11) 3089-7400

## Mexico

t (52-81) 8158-8400